



PureStyle Intelligent Color Powercore, RGBA



PureStyle Intelligent Color Powercore, RGBA, 30° x 60°, 305 mm (12 in), Medium Beam Angle

PureStyle Intelligent Color Powercore, RGBA, 30° x 60°, 305 mm (12 in), Medium Beam Angle

Innovative PureStyle Powercore luminaires bring lighting professionals high output in a compact, easily concealed luminaire. PureStyle delivers exceptionally high-quality light for a wide range of interior applications from cove to wall-washing to backlighting and beyond. Here are just some of the powerful advantages that PureStyle brings to lighting professionals and their clients.

Product data

General information	
Light source color	RGBA
Optic type	Medium beam
Optical cover/lens type	Polycarbonate bowl/cover
Luminaire light beam spread	30° x 60°
CE mark	CE mark
UL mark	UL and cUL mark
Operating and electrical	
Input Voltage	100 to 277 V


Mechanical and housing	
Housing Material	Aluminum extruded
Length	305 mm
Color	White
Approval and application	
Ingress protection code	IP20 [Finger-protected]
Energy Efficiency Class	G
FCC mark	FCC Class B
EPREL Registration Number	887776

PureStyle Intelligent Color Powercore, RGBA

Initial performance (IEC compliant)	
Initial luminous flux (system flux)	481 lm
Initial LED luminaire efficacy at RGB operation	39 lm/W
Initial input power	13 W
Over time performance (IEC compliant)	
Lumen Maintenance 50% at 25°C Calculated	72300
Lumen Maintenance 50% at 25°C Reported	47100
Lumen Maintenance 50% at 50°C Calculated	72300
Lumen Maintenance 50% at 50°C Reported	47100
Application conditions	
Ambient temperature range	-20 to +50 °C
Product data	
Full product code	871829139155599

Order product name	SA500X 30X60 RGBA L305
EAN/UPC - Product	8718291391555
Order code	123-000026-01
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	20
Material Nr. (12NC)	912400133455
Net Weight (Piece)	0.485 kg
Catalog Number	123-000026-01
Catalog Number Description	PureStyle Intelligent Color Powercore, RGBA, 30° x 60°, 305 mm (12 in), Medium Beam Angle

Dimensional drawing



SA500X 30X60 RGBA L305

