



iColor Accent Compact



iColor Accent Compact, RGB, 609 mm (24 in), Clear Lens

iColor Accent Compact, RGB, 609 mm (24 in), Clear Lens

iColor Accent Compact is a direct view linear LED luminaire ideally suited for displaying large-scale video, graphics, and intricately designed effects in a host of architectural settings. iColor Accent Compact accepts Ethernet input from the PDS-400 48V EO to support long control runs not subject to DMX data and addressing limitations. Two lens choices are available for iColor Accent Compact: a clear lens which delivers the brightest output and a translucent lens which provides the widest viewing angle.

Product data

General information	
Light source color	RGB
Optical cover/lens type	Polycarbonate bowl/cover UV-resistant
Luminaire light beam spread	105°
Light technical	
On-axis intensity in candela	94
Mechanical and housing	
Length	610 mm
Color	Aluminum
Approval and application	
Energy Efficiency Class	G


Vibration Standard	Complies with ANSI C136.31, 3G
Corrosion Resistance	Complies with ASTM B117 standard for > 1,500 hours
FCC mark	FCC Class A
Vibration Rating	Complies with ANSI C136.31, 3G
EPREL Registration Number	1081403
Initial performance (IEC compliant)	
Initial input power	16 W
Over time performance (IEC compliant)	
Lumen Maintenance 50% at 25°C Reported	60000
Lumen Maintenance 50% at 50°C Reported	60000
Lumen Maintenance 70% at 25°C Reported	60000

iColor Accent Compact


Lumen Maintenance 70% at 50°C Reported 60000	
Product data	
Full product code	871829139184599
Order product name	BCS425 RGB CL ETH L610 PP19
EAN/UPC - Product	8718291391845
Order code	101-000200-04
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	9
Material Nr. (12NC)	912400133775
Net Weight (Piece)	0.910 kg
Catalog Number	101-000200-04
Catalog Number Description	iColor Accent Compact, RGB, 609 mm (24 in), Clear Lens

Dimensional drawing



BCS425 RGB CL ETH L610 PP19



BCS425 RGB CL ETH L610 PP19

