



# iColor Accent Compact



## iColor Accent Compact, RGB, 1220 mm (48 in), Translucent Lens

iColor Accent Compact, RGB, 1220 mm (48 in), Translucent Lens

iColor Accent Compact is a direct view linear LED luminaire ideally suited for displaying large-scale video, graphics, and intricately designed effects in a host of architectural settings. iColor Accent Compact accepts Ethernet input from the PDS-400 48V EO to support long control runs not subject to DMX data and addressing limitations. Two lens choices are available for iColor Accent Compact: a clear lens which delivers the brightest output and a translucent lens which provides the widest viewing angle.

### Product data

<b>General information</b>	
Light source color	RGB
Optical cover/lens type	Polycarbonate bowl/cover UV-resistant
Luminaire light beam spread	105°
<b>Light technical</b>	
On-axis intensity in candela	188
<b>Mechanical and housing</b>	
Length	1220 mm
Color	Aluminum
<b>Approval and application</b>	
Energy Efficiency Class	G


Vibration Standard	Complies with ANSI C136.31, 3G
Corrosion Resistance	Complies with ASTM B117 standard for > 1,500 hours
FCC mark	FCC Class A
Vibration Rating	Complies with ANSI C136.31, 3G
EPREL Registration Number	1081404
<b>Initial performance (IEC compliant)</b>	
Initial input power	28 W
<b>Over time performance (IEC compliant)</b>	
Lumen Maintenance 50% at 25°C Reported	60000
Lumen Maintenance 50% at 50°C Reported	60000
Lumen Maintenance 70% at 25°C Reported	60000

iColor Accent Compact


Lumen Maintenance 70% at 50°C Reported 60000	
Product data	
Full product code	871829139185299
Order product name	BCS425 RGB CL ETH L1220 PP19
EAN/UPC - Product	8718291391852
Order code	101-000200-05

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	9
Material Nr. (12NC)	912400133776
Net Weight (Piece)	1.530 kg
Catalog Number	101-000200-05

Dimensional drawing



BCS425 RGB CL ETH L1220 PP19



BCS425 RGB CL ETH L1220 PP19

