



Vaya Flood LP

BCP432 3000 100-240 10 UL

Narrow beam angle 10°

Vaya Flood LP (gen2) is a reliable and cost effective LED flood lighting solution for both interior and exterior use that minimizes the initial investment, while providing exceptional flexibility to create eye-catching flood, wash and accent lighting effects. A wide choice of beam angles and color options let you bring a property to life with either static or dynamically changing colors. Extended light throw and high efficacy set this compact & robust luminaire apart. Its integrated power and adjustable tilt angle make this product versatile and easy to use.

Product data

General Information		Controls and Dimming	
Lamp family code	LED-HB [LED High Brightness]	Dimmable	Yes
Light source color	Neutral white		
Light source replaceable	No	Mechanical and Housing	
Driver included	Yes	Housing Material	Aluminum die cast
Optical cover/lens type	Tempered glass	Optic material	Glass
Luminaire light beam spread	10°	Optical cover/lens material	Tempered glass
Protection class IEC	Safety class I	Optical cover/lens shape	Flat
UL mark	UL and cUL mark	Optical cover/lens finish	Clear
Optic type outdoor	Narrow beam angle 10°	Color	Dark gray
PSE mark	No		
FCC mark	FCC Class A	Approval and Application	
Angle	10°	Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
		Mech. impact protection code	IK06 [1 J]
Operating and Electrical		Vibration Standard	Complies with ANSI C136.31
Input Voltage	100 to 240 V	Vibration Rating	Complies with ANSI C136.31
Input Frequency	50 to 60 Hz		

Vaya Flood LP

Initial Performance (IEC Compliant)	
Initial luminous flux (system flux)	3483 lm
Initial LED luminaire efficacy	81.4 lm/W
Init. Corr. Color Temperature	3000 K
Init. Color Rendering Index	82
Initial input power	44 W

Over Time Performance (IEC Compliant)	
Lumen Maintenance 70% at 25°C Calculated	71000
Lumen Maintenance 70% at 25°C Reported	60000
Lumen Maintenance 70% at 40°C Calculated	71000
Lumen Maintenance 70% at 40°C Reported	60000
Lumen Maintenance 80% at 25°C Calculated	45000
Lumen Maintenance 80% at 25°C Reported	45000
Lumen Maintenance 80% at 40°C Calculated	45000
Lumen Maintenance 80% at 40°C Reported	45000
Lumen Maintenance 90% at 25°C Calculated	23000
Lumen Maintenance 90% at 25°C Reported	23000


Lumen Maintenance 90% at 40°C Calculated	23000
Lumen Maintenance 90% at 40°C Reported	23000

Application Conditions	
Ambient temperature range	-40 to +40 °C

Product Data	
Full product code	871829164742399
Order product name	BCP432 3000 100-240 10 UL
EAN/UPC - Product	8718291647423
Order code	912400133928
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	912400133928
Net Weight (Piece)	2.770 kg



Dimensional drawing



Vaya

