



Vaya Flood LP

BCP432 4000 100-240 10 UL HMA

Housing with medium-length arm - Narrow beam angle 10°

Vaya Flood LP (gen2) is a reliable and cost effective LED flood lighting solution for both interior and exterior use that minimizes the initial investment, while providing exceptional flexibility to create eye-catching flood, wash and accent lighting effects. A wide choice of beam angles and color options let you bring a property to life with either static or dynamically changing colors. Extended light throw and high efficacy set this compact & robust luminaire apart. Its integrated power and adjustable tilt angle make this product versatile and easy to use.

Product data

General Information		Controls and Dimming	
Lamp family code	LED-HB [LED High Brightness]	Dimmable	Yes
Light source color	Neutral white		
Light source replaceable	No		
Driver included	Yes		
Optical cover/lens type	Tempered glass		
Luminaire light beam spread	10°		
Protection class IEC	Safety class I		
UL mark	UL and cUL mark		
Optic type outdoor	Narrow beam angle 10°		
PSE mark	No		
FCC mark	FCC Class A		
Angle	10°		
Operating and Electrical		Mechanical and Housing	
Input Voltage	100 to 240 V	Housing configuration	Housing with medium-length arm
Input Frequency	50 to 60 Hz	Housing Material	Aluminum die cast
		Optic material	Glass
		Optical cover/lens material	Tempered glass
		Optical cover/lens shape	Flat
		Optical cover/lens finish	Clear
		Color	Dark gray
		Approval and Application	
		Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
		Mech. impact protection code	IK06 [1 J]
		Vibration Standard	Complies with ANSI C136.31


Vaya Flood LP

Vibration Rating	Complies with ANSI C136.31
Initial Performance (IEC Compliant)	
Initial luminous flux (system flux)	3797 lm
Initial luminous flux at color temperature of 4000 K	3797 lm
Initial LED luminaire efficacy	87.9 lm/W
Init. Corr. Color Temperature	4000 K
Init. Color Rendering Index	82
Initial input power	44 W
Over Time Performance (IEC Compliant)	
Lumen Maintenance 70% at 25°C Calculated	71000
Lumen Maintenance 70% at 25°C Reported	60000
Lumen Maintenance 70% at 40°C Calculated	71000
Lumen Maintenance 70% at 40°C Reported	60000
Lumen Maintenance 80% at 25°C Calculated	45000
Lumen Maintenance 80% at 25°C Reported	45000
Lumen Maintenance 80% at 40°C Calculated	45000
Lumen Maintenance 80% at 40°C Reported	45000

Lumen Maintenance 90% at 25°C Calculated	23000
Lumen Maintenance 90% at 25°C Reported	23000
Lumen Maintenance 90% at 40°C Calculated	23000
Lumen Maintenance 90% at 40°C Reported	23000
Application Conditions	
Ambient temperature range	-40 to +40 °C
Product Data	
Full product code	871829164763899
Order product name	BCP432 4000 100-240 10 UL HMA
EAN/UPC - Product	8718291647638
Order code	912400133933
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	912400133933
Net Weight (Piece)	2.500 kg



Dimensional drawing



Vaya

