



# Vaya Flood LP Small

BCP432 4000 100-240 40 CE CQC PSE

Medium beam angle 40°

With budgets under pressure, property owners and developers are looking, more than ever, for value for money when it comes to capital expenditures. Vaya Flood is an affordable and reliable LED solution that minimizes the initial investment, while providing exceptional flexibility to create eye-catching, dynamic and colourful lighting effects that can bring a property to life. The robust Vaya Flood offers a wide choice of mono colours with a simple on-off switch and changing colours with a standard DMX512 controller. It is also extremely easy to install and aim.

## Product data

General Information	
Lamp family code	LED-HB [ LED High Brightness]
Lamp colour code	Neutral white
Light source replaceable	No
Driver included	Yes
Optical cover/lens type	GT [ Tempered glass]
Luminaire light beam spread	40°
Protection class IEC	Safety class I (I)
CE mark	CE mark
CQC mark	CQC-mark
Outdoor optic type	Medium beam angle 40°
PSE mark	PSE mark
Angle	40°
Operating and Electrical	
Input voltage	100 to 240 V
Input frequency	50 to 60 Hz

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Housing material	Aluminum die-cast
Optic material	Glass
Optical cover/lens material	Tempered glass
Optical cover/lens shape	Flat
Optical cover/lens finish	Clear
Colour	Dark Grey
Approval and Application	
Ingress protection code	IP66 [ Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [ 1 J]
Vibration standard	Complies with ANSI C136.31
	Complies with ANSI C136.31

Vaya Flood LP Small

Initial Performance (IEC Compliant)	
Initial luminous flux	3387 lm
Initial luminous flux at color temperature of 4000 K	3387 lm
Initial LED luminaire efficacy	85.7 lm/W
Lamp colour temperature	4000 K
Colour Rendering Index	82
Initial input power	44 W

Over Time Performance (IEC Compliant)	
Lumen Maintenance 70% at 25°C Calculated	71000
Lumen Maintenance 70% at 25°C Reported	60000
Lumen Maintenance 70% at 40°C Calculated	71000
Lumen Maintenance 70% at 40°C Reported	60000
Lumen Maintenance 80% at 25°C Calculated	45000
Lumen Maintenance 80% at 25°C Reported	45000
Lumen Maintenance 80% at 40°C Calculated	45000
Lumen Maintenance 80% at 40°C Reported	45000
Lumen Maintenance 90% at 25°C Calculated	23000


Lumen Maintenance 90% at 25°C Reported	23000
Lumen Maintenance 90% at 40°C Calculated	23000
Lumen Maintenance 90% at 40°C Reported	23000

Application Conditions	
Ambient temperature range	-40 to +40 °C

Product Data	
Full product code	871829164741699
Order product name	BCP432 4000 100-240 40 CE CQC PSE
EAN/UPC – product	8718291647416
Order code	912400133937
Numerator – quantity per pack	1
Numerator – packs per outer box	4
Material no. (12NC)	912400133937
Net weight (piece)	2.770 kg



Dimensional drawing



Vaya

