



# Vaya Flood LP

BCP432 4000 100-240 90 UL HMA

Housing with medium-length arm - Very wide beam angle 90°

Vaya Flood LP (gen2) is a reliable and cost effective LED flood lighting solution for both interior and exterior use that minimizes the initial investment, while providing exceptional flexibility to create eye-catching flood, wash and accent lighting effects. A wide choice of beam angles and color options let you bring a property to life with either static or dynamically changing colors. Extended light throw and high efficacy set this compact & robust luminaire apart. Its integrated power and adjustable tilt angle make this product versatile and easy to use.

## Product data

General Information		Controls and Dimming	
Lamp family code	LED-HB [ LED High Brightness]	Dimmable	Yes
Light source color	Neutral white		
Light source replaceable	No		
Driver included	Yes		
Optical cover/lens type	Tempered glass		
Luminaire light beam spread	90°		
Protection class IEC	Safety class I		
UL mark	UL and cUL mark		
Optic type outdoor	Very wide beam angle 90°		
PSE mark	No		
FCC mark	FCC Class A		
Angle	90°		
Operating and Electrical		Mechanical and Housing	
Input Voltage	100 to 240 V	Housing configuration	Housing with medium-length arm
Input Frequency	50 to 60 Hz	Housing Material	Aluminum die cast
		Optic material	Glass
		Optical cover/lens material	Tempered glass
		Optical cover/lens shape	Flat
		Optical cover/lens finish	Clear
		Color	Dark gray
		Approval and Application	
		Ingress protection code	IP66 [ Dust penetration-protected, jet-proof]
		Mech. impact protection code	IK06 [ 1 J]


Vaya Flood LP

Initial Performance (IEC Compliant)	
Init. Corr. Color Temperature	4000 K
Init. Color Rendering Index	82
Over Time Performance (IEC Compliant)	
Lumen Maintenance 70% at 25°C Calculated	71000
Lumen Maintenance 70% at 25°C Reported	60000
Lumen Maintenance 70% at 40°C Calculated	71000
Lumen Maintenance 70% at 40°C Reported	60000
Lumen Maintenance 80% at 25°C Calculated	45000
Lumen Maintenance 80% at 25°C Reported	45000
Lumen Maintenance 80% at 40°C Calculated	45000
Lumen Maintenance 80% at 40°C Reported	45000
Lumen Maintenance 90% at 25°C Calculated	23000
Lumen Maintenance 90% at 25°C Reported	23000
Lumen Maintenance 90% at 40°C Calculated	23000
Lumen Maintenance 90% at 40°C Reported	23000

Application Conditions	
Ambient temperature range	-40 to +40 °C
Product Data	
Full product code	871829164961899
Order product name	BCP432 4000 100-240 90 UL HMA
EAN/UPC - Product	8718291649618
Order code	912400133944
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	912400133944
Net Weight (Piece)	2.500 kg



Dimensional drawing



Vaya

