



# Vaya Flood MP Medium

BCP435 4000 220-240 40 CE CQC

Medium beam angle 40°

With budgets under pressure, property owners and developers are looking, more than ever, for value for money when it comes to capital expenditures. Vaya Flood is an affordable and reliable LED solution that minimizes the initial investment, while providing exceptional flexibility to create eye-catching, dynamic and colorful lighting effects that can bring a property to life. The robust Vaya Flood offers a wide choice of mono colors with a simple on-off switch and changing colors with a standard DMX512 controller. It is also extremely easy to install and aim.

## Product data

General Information	
Lamp family code	LED-HB [ LED High Brightness]
Light source color	Neutral white
Light source replaceable	No
Driver included	Yes
Optical cover/lens type	GT [ Tempered glass]
Luminaire light beam spread	40°
Protection class IEC	Safety class I (I)
CE mark	CE mark
CQC mark	CQC-mark
Optic type outdoor	Medium beam angle 40°
PSE mark	No
Angle	40°

## Operating and Electrical

Input Voltage	220 to 240 V
Input Frequency	50 to 60 Hz

Controls and Dimming	
Dimmable	Yes

## Mechanical and Housing

Housing Material	Aluminum die-cast
Optic material	Glass
Optical cover/lens material	Glass
Optical cover/lens shape	Flat
Optical cover/lens finish	Clear

## Approval and Application

Ingress protection code	IP66 [ Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [ 1 J]

## Initial Performance (IEC Compliant)

Initial luminous flux (system flux)	5634 lm
Initial luminous flux at color temperature of 4000 K	5634 lm
Initial LED luminaire efficacy	83.3 lm/W

Vaya Flood MP Medium

Init. Corr. Color Temperature	4000 K
Init. Color Rendering Index	82

Over Time Performance (IEC Compliant)


Lumen Maintenance 70% at 25°C Calculated	100000
Lumen Maintenance 70% at 25°C Reported	60000
Lumen Maintenance 70% at 40°C Calculated	71000
Lumen Maintenance 70% at 40°C Reported	60000
Lumen Maintenance 80% at 25°C Calculated	100000
Lumen Maintenance 80% at 25°C Reported	60000
Lumen Maintenance 80% at 40°C Calculated	45000
Lumen Maintenance 80% at 40°C Reported	45000
Lumen Maintenance 90% at 25°C Calculated	74000
Lumen Maintenance 90% at 25°C Reported	60000
Lumen Maintenance 90% at 40°C Calculated	23000
Lumen Maintenance 90% at 40°C Reported	23000

Application Conditions	
Ambient temperature range	-40 to +104 °F

Product Data	
Full product code	871829138601899
Order product name	BCP435 4000 220-240 40 CE CQC
EAN/UPC - Product	8718291386018
Order code	912400134025
Local order code	.
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2
Material Nr. (12NC)	912400134025
Net Weight (Piece)	5.720 kg



Dimensional drawing



Vaya

