



Vaya Flood MP

BCP435 4000 100 40 PSE

Medium beam angle 40°

Vaya Flood MP gen2 is a reliable and cost effective LED flood lighting solution for both interior and exterior use that minimizes the initial investment, while providing exceptional flexibility to create eye-catching flood, wash and accent lighting effects. A wide choice of beam angles and color options let you bring a property to life with either static or dynamically changing colors. Extended light throw and high efficacy set this compact & robust luminaire apart. Its integrated power and adjustable tilt angle make this product versatile and easy to use.

Product data

General Information		Controls and Dimming	
Lamp family code	LED-HB [LED High Brightness]	Dimmable	Yes
Light source color	Neutral white		
Light source replaceable	No	Mechanical and Housing	
Driver included	Yes	Housing Material	Aluminum die cast
Optical cover/lens type	Tempered glass	Optic material	Glass
Luminaire light beam spread	40°	Optical cover/lens material	Glass
Protection class IEC	Safety class I	Optical cover/lens shape	Flat
Optic type outdoor	Medium beam angle 40°	Optical cover/lens finish	Clear
PSE mark	PSE mark	Color	Dark gray
Angle	40°	Approval and Application	
Operating and Electrical		Ingress protection code	IP66 [Dust penetration-protected , jet-proof]
Input Voltage	100 V	Mech. impact protection code	IK06 [1 J]
Input Frequency	50 to 60 Hz	Vibration Standard	Complies with ANSI C136.31
		Vibration Rating	Complies with ANSI C136.31

Vaya Flood MP

Initial Performance (IEC Compliant)	
Initial luminous flux (system flux)	5634 lm
Initial luminous flux at color temperature of 4000 K	5634 lm
Initial LED luminaire efficacy	83.3 lm/W
Init. Corr. Color Temperature	4000 K
Init. Color Rendering Index	82
Initial input power	68 W

Over Time Performance (IEC Compliant)	
Lumen Maintenance 70% at 25°C Calculated	100000
Lumen Maintenance 70% at 25°C Reported	60000
Lumen Maintenance 70% at 40°C Calculated	71000
Lumen Maintenance 70% at 40°C Reported	60000
Lumen Maintenance 80% at 25°C Calculated	100000
Lumen Maintenance 80% at 25°C Reported	60000
Lumen Maintenance 80% at 40°C Calculated	45000
Lumen Maintenance 80% at 40°C Reported	45000
Lumen Maintenance 90% at 25°C Calculated	74000


Lumen Maintenance 90% at 25°C Reported	60000
Lumen Maintenance 90% at 40°C Calculated	23000
Lumen Maintenance 90% at 40°C Reported	23000

Application Conditions	
Ambient temperature range	-40 to +40 °C

Product Data	
Full product code	871829138633999
Order product name	BCP435 4000 100 40 PSE
EAN/UPC - Product	8718291386339
Order code	912400134057
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2
Material Nr. (12NC)	912400134057
Net Weight (Piece)	5.720 kg



Dimensional drawing



Vaya

