



# eW Graze MX Powercore

**eW Graze MX Powercore, 3000 K, 15° x 30° Beam Angle, 1220 mm (4 ft)**

eW Graze MX Powercore, 3000 K, 15° x 30° Beam Angle, 1220 mm (4 ft)

Many architectural structures need a linear fixture capable of illuminating multiple storeys with minimal setback. Property owners/end users need a controllable product capable of dynamic illumination to draw attention to their establishments and emphasise their brands. Graze MX Powercore is capable of illuminating over 20 meters at very close setback distances. Powercore technology enables simple installation and long product run lengths.

## Product data

| General information           |                               | Operating and electrical    |                   |
|-------------------------------|-------------------------------|-----------------------------|-------------------|
| Lamp family code              | LED-HB [ LED High Brightness] | Input Voltage               | 100 to 277 V      |
| Lamp colour code              | Neutral white                 | Input frequency             | 50 to 60 Hz       |
| Light source replaceable      | No                            | Controls and dimming        |                   |
| Driver included               | Yes                           | Dimmable                    | Yes               |
| Luminaire light beam spread   | 15° x 30°                     | Mechanical and housing      |                   |
| Protection class IEC          | Safety class I (I)            | Housing material            | Aluminum extruded |
| CE mark                       | CE mark                       | Optical cover/lens material | Polycarbonate     |
| UL mark                       | UL and cUL mark               | Length                      | 1219 mm           |
| Lifetime to 50% luminous flux | 60000 h                       |                             |                   |
| Lifetime to 70% luminous flux | 60000 h                       |                             |                   |

eW Graze MX Powercore

|                          |  |
|--------------------------|--|
| Approval and application |  |
| Ingress protection code  | IP66 [ Dust penetration-protected, jet-proof]  |
| Vibration standard       | Not compliant to ANSI C136.31, 3G. Special orders are available to conform to the standard. Please contact your Color Kinetics Lighting Sales rep for custom configurations. |
| FCC mark                 | FCC Class A  |
| Vibration rating         | Not compliant to ANSI C136.31, 3G. Special orders are available to conform to the standard. Please contact your Color Kinetics Lighting Sales rep for custom configurations. |

|                                     |        |
|-------------------------------------|--------|
| Initial performance (IEC compliant) |        |
| Lamp colour temperature             | 3000 K |
| Colour Rendering Index              | >80    |
| Initial input power                 | 60 W   |

|                                       |       |
|---------------------------------------|-------|
| Over time performance (IEC compliant) |       |
| Lumen Maintenance 50% at 25 °C        | 60000 |
| Reported                              |       |
| Lumen Maintenance 50% at 50 °C        | 60000 |
| Reported                              |       |
| Lumen Maintenance 70% at 25 °C        | 60000 |
| Reported                              |       |

|                                |       |
|--------------------------------|-------|
| Lumen Maintenance 70% at 50 °C | 60000 |
| Reported                       |       |

|                           |               |
|---------------------------|---------------|
| Application conditions    |               |
| Ambient temperature range | -20 to +50 °C |

|                                   |   |
|-----------------------------------|---|
| Product data                      |   |
| Full product code                 | 871829139586700   |
| Order product name                | BCS419 15x30-3000 L1219   |
| EAN/UPC – product                 | 8718291395867   |
| Order code                        | 523-000080-77   |
| SAP numerator – quantity per pack | 1   |
| Numerator – packs per outer box   | 1   |
| SAP material                      | 912400135130  |
| Net Weight (Piece)                | 6.200 kg  |
| Commercial Code                   | 523-000080-77   |
| Catalogue number description      | eW Graze MX Powercore, 3000 K, 15° x 30° Beam Angle, 1220 mm (4 ft) |



Dimensional drawing

