



# Vaya Cove LP G2

## Vaya Cove LP G2, 3000 K, 305 mm (1 ft), UL/CE

Vaya Cove LP G2, 3000 K, 305 mm (1 ft), UL/CE

Vaya Cove LP G2 is a reliable cost-effective LED luminaire offering crisp white light for interior use. Designed for linear cove and accent lighting applications this luminaire offers a very low profile and integrated connectors to eliminate socket shadows. Vaya Cove LP offers on/off control or dimming via the use of any standard 0-10 V or DALI dimming controller.

### Product data

<b>General information</b>		<b>Optical cover/lens material</b>		Polycarbonate
Lamp family code	LED-HB [ LED High Brightness]	<b>Optical cover/lens finish</b>		Clear
Beam angle of light source	110 °	<b>Length</b>		300 mm
Light source colour	Neutral white	<b>Colour</b>		White
Light source replaceable	No	<b>Approval and application</b>		
Driver included	No	<b>Ingress protection code</b>		IP40 [ Wire-protected]
Luminaire light beam spread	110°	<b>Initial performance (IEC compliant)</b>		
CE mark	CE mark	<b>Initial luminous flux (system flux)</b>		274 lm
UL mark	UL and cUL mark	<b>Initial LED luminaire efficacy</b>		103 lm/W
<b>Operating and electrical</b>		<b>Init. Corr. Colour Temperature</b>		3000 K
Input Voltage	24 V	<b>Init. Colour rendering index</b>		≥80
Control signal voltage	1-10 V DC	<b>Initial input power</b>		2.7 W
<b>Controls and dimming</b>		<b>Over time performance (IEC compliant)</b>		
Dimmable	Yes	<b>Lumen Maintenance 70% at 25 °C Calculated</b>		100000
<b>Mechanical and housing</b>		<b>Lumen Maintenance 70% at 25 °C Reported</b>		60000
Housing material	Polycarbonate	<b>Lumen Maintenance 70% at 50 °C Calculated</b>		100000
Optic material	Polycarbonate	<b>Lumen Maintenance 70% at 50 °C Reported</b>		60000

Vaya Cove LP G2

Lumen Maintenance 80% at 25 °C Calculated	100000
Lumen Maintenance 80% at 25 °C Reported	60000
Lumen Maintenance 80% at 50 °C Calculated	97000
Lumen Maintenance 80% at 50 °C Reported	60000
Lumen Maintenance 90% at 25 °C Calculated	56000
Lumen Maintenance 90% at 25 °C Reported	56000
Lumen Maintenance 90% at 50 °C Calculated	45000
Lumen Maintenance 90% at 50 °C Reported	45000

Application conditions

Ambient temperature range	-20 to +50 °C
---------------------------	---------------


Product data

Full product code	871869921299599
-------------------	-----------------

Order product name	SM452L 3000 24V L300 CE UL
EAN/UPC – product	8718699212995
Order code	350-000017-06
SAP numerator – quantity per pack	1
Numerator – packs per outer box	30
SAP material	912400135341
Net Weight (Piece)	0.090 kg
Commercial Code	350-000017-06
Catalogue number description	Vaya Cove LP G2, 3000 K, 305 mm (1 ft), UL/CE



Dimensional drawing



SM452L 3000 24V L300 CE UL

