



ColorBurst IntelliHue Powercore



ColorBurst IntelliHue Powercore, 8° Native (no spread lens), Gray Housing, Landscape

ColorBurst IntelliHue Powercore, 8° Native (no spread lens), Gray Housing, Landscape

ColorBurst IntelliHue Powercore produces high-quality white, pastel, and saturated color light, in the same precisely controllable luminaire for outdoor wall washing and spot lighting applications. IntelliHue technology delivers exceptional CRI and the ability to choose any CCT between 2000 K and 10000 K.

Product data

General information		Light technical	
Beam angle of light source	8 °	Efficacy (lm/W) @ 4000 K	46.9 lm/W
Light source color	IntelliHue	Efficacy (lm/W) @ 2700 K	49 lm/W
Light source replaceable	No	CRI @ 4000 K	85
Driver/power unit/transformer	-	Operating and electrical	
Driver included	Yes	Input Voltage	100 to 277 V
Optical cover/lens type	Tempered glass	Input Frequency	50 to 60 Hz
Luminaire light beam spread	8°	Controls and dimming	
Protection class IEC	Safety class I	Dimmable	Yes
CE mark	CE mark	Mechanical and housing	
Glare shielding accessories	Honeycomb louver	Housing configuration	Housing with medium-length arm
Glasses	-	Housing Material	Aluminum die cast
Angle	8°		


ColorBurst IntelliHue Powercore

Color	Gray
Approval and application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Energy Efficiency Class	G
Mech. impact protection code	IK08 [5 J vandal-protected]
Corrosion Resistance	Complies with ASTM B117 standard for > 1,500 hours
EPREL Registration Number	887792
Initial performance (IEC compliant)	
Initial luminous flux (system flux)	1481 lm
Initial LED luminaire efficacy	47 lm/W
Init. Corr. Color Temperature	- K
Init. Color Rendering Index	≥80
Initial input power	33 W
Over time performance (IEC compliant)	
Lumen Maintenance 70% at 25°C Calculated	48300
Lumen Maintenance 70% at 50°C Calculated	48300
Lumen Maintenance 80% at 25°C Calculated	48300

Lumen Maintenance 80% at 50°C Calculated	48300
Lumen Maintenance 90% at 25°C Reported	27000
Lumen Maintenance 90% at 50°C Reported	25000
Application conditions	
Ambient temperature range	-40 to +50 °C
Product data	
Full product code	871869921144899
Order product name	BCP462 G2 19xLED-HB/RGBMW HMA GR
EAN/UPC - Product	8718699211448
Order code	423-000003-20
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2
Material Nr. (12NC)	912400135469
Net Weight (Piece)	3.470 kg
Catalog Number	423-000003-20
Catalog Number Description	ColorBurst IntelliHue Powercore, 8° Native (no spread lens), Gray Housing, Landscape



Dimensional drawing



BCP462 G2 19xLED-HB/RGBMW HMA GR

