



eW Flex Compact

eW Flex Compact, 2700 K, Narrow Beam Lens, Black Housing, 4 in on-center node spacing

eW Flex Compact, 2700 K, Narrow Beam Lens, Black Housing, 4 in on-center node spacing

eW Flex Compact is a versatile strand of large, individually controllable white-light LED nodes. The flexible form factor allows dynamic points of white light to be installed across almost any interior or exterior surface, including walls, ceilings, floors, and three-dimensional sculptures. eW Flex Compact can also be used to light tight alcove spaces and signage.

Product data

General information		Controls and dimming	
Lamp family code	LED-MD [LED Multi-die]	Dimmable	Yes
Light source replaceable	No		
Driver included	No		
Optical cover/lens type	PC-UV [Polycarbonate bowl/cover UV-resistant]	Mechanical and housing	
CE mark	CE mark	Housing material	Polycarbonate
UL mark	UL mark	Optic material	Polycarbonate
		Colour	Black
		Approval and application	
Light technical		Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Luminance per node	122240 cd/m²	Mech. impact protection code	IK10 [20 J vandal-resistant]
Luminous intensity (peak value) on beam axis per node	85.5 cd	FCC mark	FCC Class A
Operating and electrical		Initial performance (IEC compliant)	
Input Voltage	24 V	Initial luminous flux at colour temperature of 2,700 K	73 lm

eW Flex Compact

Init. Corr. Colour Temperature	2700 K
Initial input power	1 W

Over time performance (IEC compliant)

Lumen Maintenance 70% at 25 °C Calculated	56000
Lumen Maintenance 70% at 25 °C Reported	56000
Lumen Maintenance 70% at 50 °C Calculated	56000
Lumen Maintenance 70% at 50 °C Reported	56000
Lumen Maintenance 80% at 25 °C Calculated	37000
Lumen Maintenance 80% at 25 °C Reported	37000
Lumen Maintenance 80% at 50 °C Calculated	37000
Lumen Maintenance 80% at 50 °C Reported	37000
Lumen Maintenance 90% at 25 °C Calculated	20000
Lumen Maintenance 90% at 25 °C Reported	20000
Lumen Maintenance 90% at 50 °C Calculated	20000
Lumen Maintenance 90% at 50 °C Reported	20000

Application conditions

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Product data	
Full product code	871869921406799
Order product name	BGC481 50 2700K NRRW BK P102
EAN/UPC – product	8718699214067
Order code	500-000012-57
SAP numerator – quantity per pack	1
Numerator – packs per outer box	6
SAP material	912400135783
Net Weight (Piece)	1.740 kg
Commercial Code	500-000012-57
Catalogue number description	eW Flex Compact, 2700 K, Narrow Beam Lens, Black Housing, 4 in on-center node spacing

