

eW Flex Compact

eW Flex Compact, 5000 K, Narrow Beam Lens, White Housing, 12 in on-center node spacing

eW Flex Compact, 5000 K, Narrow Beam Lens, White Housing, 12 in on-center node spacing

eW Flex Compact is a versatile strand of large, individually controllable white-light LED nodes. The flexible form factor allows dynamic points of white light to be installed across almost any interior or exterior surface, including walls, ceilings, floors, and three-dimensional sculptures. eW Flex Compact can also be used to light tight alcove spaces and signage.

Product data

General Information		Optic material	
Lamp family code	LED-MD [LED Multi-die]	Polycarbonate	
Light source replaceable	No	Colour	
Driver included	No	White	
Optical cover/lens type	PC-UV [Polycarbonate bowl/cover UV-resistant]	Approval and Application	
CE mark	CE mark	Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
UL mark	UL mark	Mech. impact protection code	IK10 [20 J vandal-resistant]
Operating and Electrical		Initial Performance (IEC Compliant)	
Input Voltage	24 V	Init. Corr. Colour Temperature	5000 K
Controls and Dimming		Initial input power	1 W
Dimmable	Yes	Over Time Performance (IEC Compliant)	
Mechanical and Housing		Lumen Maintenance 70% at 25 °C Calculated	56000
Housing material	Polycarbonate	Lumen Maintenance 70% at 25 °C Reported	56000
		Lumen Maintenance 70% at 50 °C Calculated	56000
		Lumen Maintenance 70% at 50 °C Reported	56000

eW Flex Compact

Lumen Maintenance 80% at 25 °C Calculated	37000
Lumen Maintenance 80% at 25 °C Reported	37000
Lumen Maintenance 80% at 50 °C Calculated	37000
Lumen Maintenance 80% at 50 °C Reported	37000
Lumen Maintenance 90% at 25 °C Calculated	20000
Lumen Maintenance 90% at 25 °C Reported	20000
Lumen Maintenance 90% at 50 °C Calculated	20000
Lumen Maintenance 90% at 50 °C Reported	20000

Application Conditions

Ambient temperature range	-40 to +50 °C
---------------------------	---------------


Product Data

Full product code	871869921423499
-------------------	-----------------

Order product name	BGC481 50 5000K NRRW WH P305
EAN/UPC – product	8718699214234
Order code	500-000012-78
SAP numerator – quantity per pack	1
Numerator – packs per outer box	6
SAP material	912400135805
SAP net weight (piece)	1.740 kg
Commercial Code	500-000012-78
Catalogue number description	eW Flex Compact, 5000 K, Narrow Beam Lens, White Housing, 12 in on-center node spacing



Dimensional drawing



eW Flex Compact

