



# eW Flex Compact

## eW Flex Compact, 5000 K, Narrow Beam Lens, Black Housing, 12 in on-center node spacing

eW Flex Compact, 5000 K, Narrow Beam Lens, Black Housing, 12 in on-center node spacing

eW Flex Compact is a versatile strand of large, individually controllable white-light LED nodes. The flexible form factor allows dynamic points of white light to be installed across almost any interior or exterior surface, including walls, ceilings, floors, and three-dimensional sculptures. eW Flex Compact can also be used to light tight alcove spaces and signage.

### Product data

General Information			
Lamp family code	LED-MD [ LED Multi-die]	Optic material	Polycarbonate
Light source replaceable	No	Colour	Black
Driver included	No	Approval and Application	
Optical cover/lens type	PC-UV [ Polycarbonate bowl/cover UV-resistant]	Ingress protection code	IP66 [ Dust penetration-protected, jet-proof]
CE mark	CE mark	Mech. impact protection code	IK10 [ 20 J vandal-resistant]
UL mark	UL mark	Initial Performance (IEC Compliant)	
Operating and Electrical		Init. Corr. Colour Temperature	5000 K
Input Voltage	24 V	Initial input power	1 W
Controls and Dimming		Over Time Performance (IEC Compliant)	
Dimmable	Yes	Lumen Maintenance 70% at 25 °C Calculated	56000
Mechanical and Housing		Lumen Maintenance 70% at 25 °C Reported	56000
Housing material	Polycarbonate	Lumen Maintenance 70% at 50 °C Calculated	56000
		Lumen Maintenance 70% at 50 °C Reported	56000

eW Flex Compact

Lumen Maintenance 80% at 25 °C Calculated	37000
Lumen Maintenance 80% at 25 °C Reported	37000
Lumen Maintenance 80% at 50 °C Calculated	37000
Lumen Maintenance 80% at 50 °C Reported	37000
Lumen Maintenance 90% at 25 °C Calculated	20000
Lumen Maintenance 90% at 25 °C Reported	20000
Lumen Maintenance 90% at 50 °C Calculated	20000
Lumen Maintenance 90% at 50 °C Reported	20000

Application Conditions

Ambient temperature range	-40 to +50 °C
---------------------------	---------------


Product Data

Full product code	871869921424199
-------------------	-----------------

Order product name	BGC481 50 5000K NRRW BK P305
EAN/UPC – product	8718699214241
Order code	500-000012-79
SAP numerator – quantity per pack	1
Numerator – packs per outer box	6
SAP material	912400135806
SAP net weight (piece)	1.740 kg
Commercial Code	500-000012-79
Catalogue number description	eW Flex Compact, 5000 K, Narrow Beam Lens, Black Housing, 12 in on-center node spacing



Dimensional drawing



eW Flex Compact

