



eW Profile Powercore gen4

eW Profile Powercore gen4, 3500 K, 120 VAC, 235 mm (9.25 in)

eW Profile Powercore gen4, 3500 K, 120 VAC, 235 mm (9.25 in)

Profile gen4 brings advanced under-cabinet lighting to today's sophisticated kitchens. Thanks to its ultra-low profile, Profile gen4 fits seamlessly into any kitchen – from galley to grand, including retrofits and new constructions. To create the right ambience, it offers four popular colour temperatures (2,700 K, 3,000 K, 3,500 K or 4,000 K). A choice of luminaire lengths and a wide range of accessories keep installation fast and easy. Exceptional energy-efficiency can generate rebates right from the start, and deliver dramatic energy savings over many years of reliable use.

Product data


| General information | | | |
|---|--------------------------------|---|--------|
| Optic type | WB [Wide beam] | Lumen Maintenance 50% at 25 °C Reported | 60000 |
| Optical cover/lens type | PC [Polycarbonate bowl/cover] | Lumen Maintenance 50% at 50 °C Calculated | 100000 |
| Luminaire light beam spread | 105° | Lumen Maintenance 50% at 50 °C Reported | 60000 |
| Mechanical and housing | | Lumen Maintenance 70% at 25 °C Calculated | 100000 |
| Colour | White | Lumen Maintenance 70% at 25 °C Reported | 60000 |
| Initial performance (IEC compliant) | | Lumen Maintenance 70% at 50 °C Calculated | 100000 |
| Init. Corr. Colour Temperature | 3500 K | Lumen Maintenance 70% at 50 °C Reported | 60000 |
| Initial input power | 2.7 W | Lumen Maintenance 80% at 25 °C Calculated | 86000 |
| Over time performance (IEC compliant) | | Lumen Maintenance 80% at 25 °C Reported | 60000 |
| Lumen Maintenance 50% at 25 °C Calculated | | Lumen Maintenance 80% at 50 °C Calculated | 65000 |
| | | Lumen Maintenance 80% at 50 °C Reported | 60000 |
| | | Lumen Maintenance 90% at 25 °C Calculated | 41000 |
| | | Lumen Maintenance 90% at 25 °C Reported | 41000 |
| | | Lumen Maintenance 90% at 50 °C Calculated | 30000 |

eW Profile Powercore gen4

| | |
|---|--------------------------|
| Lumen Maintenance 90% at 50 °C Reported | 30000 |
| Product data | |
| Full product code | 871869921362699 |
| Order product name | BCX413 3500 120V 235L WH |
| EAN/UPC – product | 8718699213626 |
| Order code | 523-000027-93 |
| SAP numerator – quantity per pack | 1 |

| | |
|---------------------------------|--|
| Numerator – packs per outer box | 10 |
| SAP material | 912400135966 |
| Net Weight (Piece) | 0.276 kg |
| Commercial Code | 523-000027-93 |
| Catalogue number description | eW Profile Powercore gen4, 3500 K, 120 VAC, 235 mm (9.25 in) |

Dimensional drawing



BCX413 3500 120V 235L WH

