



SofTrace Recessed Fluorescent

2STG228-D-UNV

2x4, 2 Lamp F28T5, Diffuse (Ribbed) Center Diffuser

SofTrace brings new meaning to the concept of combining style with performance. Equipped with a fresh streamlined design and innovative technology, SofTrace provides a huge step forward for the lighting industry. The sleek profile design belies the true “horsepower under the hood”. With efficiency levels exceeding 95% and lumens per Watt as great as 87, an architectural product now delivers leading edge performance for the most environmentally conscious user.

Product data

| General Information | |
|-------------------------------|---------------|
| Lamp Envelope Code | T-5 |
| Lamp Source Code | Fluorescent |
| Lamp Watts | 28 |
| Number of Lamps | 2 |
| Photometric Distribution Type | Direct |
| Mounting | Recessed |
| Operating and Electrical | |
| Voltages | 120/277/347 V |
| Mechanical and Housing | |
| Fixture Size | 2 ft x 4 ft |

| Product Data | |
|---------------------------------|---|
| Order product name | 2STG228-D-UNV |
| EAN/UPC - Product | 734340072617 |
| Order code | 912400342596 |
| Local order code | 4007261 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 1 |
| Material Nr. (12NC) | 912400342596 |
| Net Weight (Piece) | 0.001 kg |
| Commercial Code | 2STG228-D-UNV-1/2-EB95-LPT835 |
| Catalog Number Description | 2x4, 2 Lamp F28T5, Diffuse (Ribbed) Center Diffuser |
| Quick Ship | - |