



# SofTrace Recessed Fluorescent

## 2x4, 2 Lamp F28T5, Diffuse (Ribbed) Center Diffuser

2x4, 2 Lamp F28T5, Diffuse (Ribbed) Center Diffuser

SofTrace brings new meaning to the concept of combining style with performance. Equipped with a fresh streamlined design and innovative technology, SofTrace provides a huge step forward for the lighting industry. The sleek profile design belies the true “horsepower under the hood”. With efficiency levels exceeding 95% and lumens per Watt as great as 87, an architectural product now delivers leading edge performance for the most environmentally conscious user.

### Product data

General Information	
Lamp Envelope Code	T-5
Lamp Source Code	Fluorescent
Lamp Watts	28
Number of Lamps	2
Photometric Distribution Type	Direct
Mounting	Recessed
Operating and Electrical	
Voltages	120/277/347 V
Mechanical and Housing	
Fixture Size	2 ft x 4 ft

Product Data	
Order product name	2STG228-D-UNV
EAN/UPC - Product	734340072617
Order code	2STG228-D-UNV-1/2-EB95-LPT835
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400342596
Net Weight (Piece)	0.001 kg
Catalog Number	2STG228-D-UNV-1/2-EB95-LPT835
Catalog Number Description	2x4, 2 Lamp F28T5, Diffuse (Ribbed) Center Diffuser