



SofTrace Recessed Fluorescent

2x4, 2 Lamp F28T5, Round Perforated w/White Overlay Center Diffuser

2x4, 2 Lamp F28T5, Round Perforated w/White Overlay Center Diffuser

SofTrace brings new meaning to the concept of combining style with performance. Equipped with a fresh streamlined design and innovative technology, SofTrace provides a huge step forward for the lighting industry. The sleek profile design belies the true “horsepower under the hood”. With efficiency levels exceeding 95% and lumens per Watt as great as 87, an architectural product now delivers leading edge performance for the most environmentally conscious user.

Product data

General Information		Mechanical and Housing	
Lamp Envelope Code	T-5	Fixture Size	2 ft x 4 ft
Lamp Source Code	Fluorescent	Product Data	
Lamp Watts	28	Order product name	2STG228-PMW-UNV
Number of Lamps	2	EAN/UPC - Product	734340125047
Photometric Distribution Type	Direct	Order code	2STG228-PMW-UNV-1/2-EB
Mounting	Recessed	Numerator - Quantity Per Pack	1
Operating and Electrical		Numerator - Packs per outer box	1
Voltages	120/277/347 V	Material Nr. (12NC)	912400342887
Luminaire Input Watts	60	Net Weight (Piece)	0.001 kg
		Catalog Number	2STG228-PMW-UNV-1/2-EB

SofTrace Recessed Fluorescent

Catalog Number	Description
	2x4, 2 Lamp F28T5, Round Perforated w/White Overlay Center Diffuser

