



SofTrace Recessed Fluorescent

2STG228-D-UNV

2x4, 2 Lamp F28T5, Diffuse (Ribbed) Center Diffuser

SofTrace brings new meaning to the concept of combining style with performance. Equipped with a fresh streamlined design and innovative technology, SofTrace provides a huge step forward for the lighting industry. The sleek profile design belies the true “horsepower under the hood”. With efficiency levels exceeding 95% and lumens per Watt as great as 87, an architectural product now delivers leading edge performance for the most environmentally conscious user.

Product data

General Information	
Lamp Envelope Code	T-5
Lamp Source Code	Fluorescent
Lamp Watts	28
Number of Lamps	2
Photometric Distribution Type	Direct
Mounting	Recessed
Operating and Electrical	
Voltages	120/277/347 V
Luminaire Input Watts	60
Mechanical and Housing	
Fixture Size	2 ft x 4 ft

Product Data	
Order product name	2STG228-D-UNV
EAN/UPC - Product	734340134155
Order code	912400342933
Local order code	4013415
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400342933
Net Weight (Piece)	0.001 kg
Commercial Code	2STG228-D-UNV-1/2-EB
Catalog Number Description	2x4, 2 Lamp F28T5, Diffuse (Ribbed) Center Diffuser
Quick Ship	-