



SofTrace Recessed Fluorescent

2x2, 2 Lamp F17T8, Round Perforated w/White Overlay Center Diffuser

2x2, 2 Lamp F17T8, Round Perforated w/White Overlay Center Diffuser

SofTrace brings new meaning to the concept of combining style with performance. Equipped with a fresh streamlined design and innovative technology, SofTrace provides a huge step forward for the lighting industry. The sleek profile design belies the true “horsepower under the hood”. With efficiency levels exceeding 95% and lumens per Watt as great as 87, an architectural product now delivers leading edge performance for the most environmentally conscious user.

Product data

General Information	
Lamp Envelope Code	T-8
Lamp Source Code	Fluorescent
Lamp Watts	17
Number of Lamps	2
Photometric Distribution Type	Direct
Mounting	Recessed
Operating and Electrical	
Voltages	120/277/347 V
Luminaire Input Watts	31

Mechanical and Housing	
Fixture Size	2 ft x 2 ft
Product Data	
Order product name	2STG217-PMW-UNV
EAN/UPC - Product	734340182774
Order code	2STG217-PMW-UNV-1/2-EB
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400343181
Net Weight (Piece)	0.001 kg
Catalog Number	2STG217-PMW-UNV-1/2-EB

SofTrace Recessed Fluorescent

Catalog Number	Description
	2x2, 2 Lamp F17T8, Round Perforated w/White Overlay Center Diffuser

