



SofTrace Recessed Fluorescent

2x2, 2 Lamp F14T5, Round Perforated w/White Overlay Center Diffuser

2x2, 2 Lamp F14T5, Round Perforated w/White Overlay Center Diffuser

SofTrace brings new meaning to the concept of combining style with performance. Equipped with a fresh streamlined design and innovative technology, SofTrace provides a huge step forward for the lighting industry. The sleek profile design belies the true “horsepower under the hood”. With efficiency levels exceeding 95% and lumens per Watt as great as 87, an architectural product now delivers leading edge performance for the most environmentally conscious user.

Product data

General Information		Mechanical and Housing	
Lamp Envelope Code	T-5	Fixture Size	2 ft x 2 ft
Lamp Source Code	Fluorescent	Product Data	
Lamp Watts	14	Order product name	2STG214-PMW-UNV
Number of Lamps	2	EAN/UPC - Product	734340428261
Photometric Distribution Type	Direct	Order code	2STG214-PMW-UNV-1/2-EB
Mounting	Recessed	Numerator - Quantity Per Pack	1
Operating and Electrical		Numerator - Packs per outer box	1
Voltages	120/277/347 V	Material Nr. (12NC)	912400344458
Luminaire Input Watts	34	Net Weight (Piece)	0.001 kg
		Catalog Number	2STG214-PMW-UNV-1/2-EB

SofTrace Recessed Fluorescent

Catalog Number	Description
	2x2, 2 Lamp F14T5, Round Perforated w/White Overlay Center Diffuser

