



# Arioso Recessed

## 2x2, 2 Lamp F17T8, Perforated Metal Shield w/ White Overlay

2x2, 2 Lamp F17T8, Perforated Metal Shield w/White Overlay

Arioso Recessed offers simple clean lines in combination with soft natural illumination. This series focuses on providing smooth comfortable lighting while subtly complementing the space. Flexible enough to integrate with any architectural design, Arioso Recessed provides a soft unassuming glow with comfortable illumination.

### Product data

General Information	
Lamp Envelope Code	T-8
Lamp Source Code	Fluorescent
Lamp Watts	17
Number of Lamps	2
Photometric Distribution Type	Direct
Mounting	Recessed
Operating and Electrical	
Voltages	120/277/347/UNIV V
Luminaire Input Watts	33
Mechanical and Housing	
Fixture Size	2 ft x 2 ft
Shape	Square

Product Data	
Order product name	2AVG217-PMW-UNV
EAN/UPC - Product	734340958003
Order code	2AVG217-PMW-UNV-1/2-EB
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400347177
Net Weight (Piece)	0.001 kg
Catalog Number	2AVG217-PMW-UNV-1/2-EB
Catalog Number Description	2x2, 2 Lamp F17T8, Perforated Metal Shield w/White Overlay