



# Ariosso Recessed

## 2x4, 2 Lamp F32T8, Perforated Metal Shield w/ White Overlay

2x4, 2 Lamp F32T8, Perforated Metal Shield w/White Overlay

Ariosso Recessed offers simple clean lines in combination with soft natural illumination. This series focuses on providing smooth comfortable lighting while subtly complementing the space. Flexible enough to integrate with any architectural design, Ariosso Recessed provides a soft unassuming glow with comfortable illumination.

### Product data

General Information	
Lamp Envelope Code	T-8
Lamp Source Code	Fluorescent
Lamp Watts	32
Number of Lamps	2
Photometric Distribution Type	Direct
Mounting	Recessed
Operating and Electrical	
Voltages	120/277/347/UNIV V
Luminaire Input Watts	60
Mechanical and Housing	
Fixture Size	2 ft x 4 ft
Shape	Rectangular

Product Data	
Order product name	2AVG232-PMW-UNV
EAN/UPC - Product	782343294994
Order code	2AVG232-PMW-UNV-1/2-EB10I
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400348978
Net Weight (Piece)	0.001 kg
Catalog Number	2AVG232-PMW-UNV-1/2-EB10I
Catalog Number Description	2x4, 2 Lamp F32T8, Perforated Metal Shield w/White Overlay