



SofTrace Recessed Fluorescent

2x4, 2 Lamp F54T5HO, Diffuer (Smooth) Center Diffuser

2x4, 2 Lamp F54T5HO, Diffuer (Smooth) Center Diffuser

SofTrace brings new meaning to the concept of combining style with performance. Equipped with a fresh streamlined design and innovative technology, SofTrace provides a huge step forward for the lighting industry. The sleek profile design belies the true “horsepower under the hood”. With efficiency levels exceeding 95% and lumens per Watt as great as 87, an architectural product now delivers leading edge performance for the most environmentally conscious user.

Product data

General Information	
Lamp Envelope Code	T-5
Lamp Source Code	Fluorescent
Lamp Watts	54
Number of Lamps	2
Photometric Distribution Type	Direct
Mounting	Recessed
Operating and Electrical	
Voltages	120/277/347 V
Luminaire Input Watts	116
Mechanical and Housing	
Fixture Size	2 ft x 4 ft

Product Data	
Order product name	2STG254HO-DS-UNV
EAN/UPC - Product	782343717271
Order code	2STG254HO-DS-UNV-1/2-EB
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400353297
Net Weight (Piece)	11.700 kg
Catalog Number	2STG254HO-DS-UNV-1/2-EB
Catalog Number Description	2x4, 2 Lamp F54T5HO, Diffuer (Smooth) Center Diffuser