



DuaLED Recessed

2x4, 4900 Nominal Delivered Lumens, 4000K, Diffuse

2x4, 4900 Nominal Delivered Lumens, 4000K, Diffuse - 102 lm/W

DuaLED was thoughtfully developed as a sustainable luminaire with a modern appearance and uncomplicated design, also offering exceptional quality and performance, for an outstanding benefit to the customer. DuaLED is a highly efficient, architecturally styled recessed LED luminaire designed with a minimalistic strategy to achieve sustainable objectives. It combines an extremely low profile with clean aesthetics and is powered by highly efficient advanced LED sources, providing the utmost in comfortable efficient lighting. Driver and integral control options ensure optimization for every application. Designed for excellent visual comfort, DuaLED is perfect for a wide variety of general applications like offices, schools, retail, or healthcare.

Product data

General Information	
Lamp Source Code	LED
Colour Temperature	4000K
CRI	80
Photometric Distribution Type	Direct
Mounting	Recessed

Operating and Electrical	
Voltages	120/277/347 V
Luminaire Input Watts	48

Mechanical and Housing	
Fixture Size	2 ft x 4 ft
Shape	Rectangular

Initial Performance (IEC Compliant)	
Luminaire Lumens	4900
Efficacy	102 lm/W

Product Data	
Order product name	2DLG49L840-4-D-UNV
EAN/UPC - Product	782343786635
Order code	2DLG49L840-4-D-UNV-DIM

DuaLED Recessed

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400357278
Net Weight (Piece)	0.001 kg

Catalog Number	2DLG49L840-4-D-UNV-DIM
Catalog Number Description	2x4, 4900 Nominal Delivered Lumens, 4000K, Diffuse

