



# DuaLED Recessed

## 2DLG44L835-2-D-UNV

2x2, 4400 Nominal Delivered Lumens, 3500K, Diffuse - 94 lm/W

DuaLED was thoughtfully developed as a sustainable luminaire with a modern appearance and uncomplicated design, also offering exceptional quality and performance, for an outstanding benefit to the customer. DuaLED is a highly efficient, architecturally styled recessed LED luminaire designed with a minimalistic strategy to achieve sustainable objectives. It combines an extremely low profile with clean aesthetics and is powered by highly efficient advanced LED sources, providing the utmost in comfortable efficient lighting. Driver and integral control options ensure optimization for every application. Designed for excellent visual comfort, DuaLED is perfect for a wide variety of general applications like offices, schools, retail, or healthcare.

### Product data

General Information		Initial Performance (IEC Compliant)	
Lamp Source Code	LED	Luminaire Lumens	4400
Color Temperature	3500K	Efficacy	94 lm/W
CRI	80		
Photometric Distribution Type	Direct	Product Data	
Mounting	Recessed	Order product name	2DLG44L835-2-D-UNV
		EAN/UPC - Product	782343873267
		Order code	912400363564
		Local order code	4387326
		Numerator - Quantity Per Pack	1
		Numerator - Packs per outer box	1
		Material Nr. (12NC)	912400363564
		Net Weight (Piece)	0.001 kg
		Commercial Code	2DLG44L835-2-D-UNV-DIM
		Catalog Number Description	2x2, 4400 Nominal Delivered Lumens, 3500K, Diffuse
		Quick Ship	Spec Smart (10 Days) USA
Operating and Electrical			
Voltages	120/277/347 V		
Luminaire Input Watts	47		
Mechanical and Housing			
Fixture Size	2 ft x 2 ft		
Shape	Square		

