



DuaLED Recessed

2DLG38L835-2-D-UNV

2x2, 3800 Nominal Delivered Lumens, 3500K, Diffuse - 97 lm/W

DuaLED was thoughtfully developed as a sustainable luminaire with a modern appearance and uncomplicated design, also offering exceptional quality and performance, for an outstanding benefit to the customer. DuaLED is a highly efficient, architecturally styled recessed LED luminaire designed with a minimalistic strategy to achieve sustainable objectives. It combines an extremely low profile with clean aesthetics and is powered by highly efficient advanced LED sources, providing the utmost in comfortable efficient lighting. Driver and integral control options ensure optimization for every application. Designed for excellent visual comfort, DuaLED is perfect for a wide variety of general applications like offices, schools, retail, or healthcare.

Product data

General Information	
Lamp Source Code	LED
Color Temperature	3500K
CRI	80
Photometric Distribution Type	Direct
Mounting	Recessed
Operating and Electrical	
Voltages	120/277/347 V
Luminaire Input Watts	39
Mechanical and Housing	
Fixture Size	2 ft x 2 ft
Shape	Square

Initial Performance (IEC Compliant)	
Luminaire Lumens	3800
Efficacy	97 lm/W
Product Data	
Order product name	2DLG38L835-2-D-UNV
EAN/UPC - Product	782343882276
Order code	912400364135
Local order code	4388227
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400364135
Net Weight (Piece)	0.001 kg
Commercial Code	2DLG38L835-2-D-UNV-DIM
Catalog Number Description	2x2, 3800 Nominal Delivered Lumens, 3500K, Diffuse
Quick Ship	Spec Smart (10 Days) USA

