



# SP Static Recessed Lensed

2SPG217R-FS12-UNV

2x2, 2 Lamp F17T8, Prismatic Acrylic Lens

The SP Static Lensed Troffer is a specification grade recessed lensed luminaire and offers many premium options.

## Product data

General Information	
Lamp Envelope Code	T-8
Lamp Source Code	Fluorescent
Lamp Watts	17
Number of Lamps	2
Mounting	Recessed
Operating and Electrical	
Voltages	120/277/347 V
Mechanical and Housing	
Fixture Size	2 ft x 2 ft
Product Data	
Order product name	2SPG217R-FS12-UNV

EAN/UPC - Product	781370668433
Order code	912400371389
Local order code	7066843
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400371389
Net Weight (Piece)	0.001 kg
Commercial Code	2SPG217R-FS12-UNV-1/2-EB
Catalog Number Description	2x2, 2 Lamp F17T8, Prismatic Acrylic Lens
Quick Ship	-