



SP Static Recessed Lensed

2SPG432-FS12-UNV

2x4, 4 Lamp F32T8, Prismatic Acrylic Lens

The SP Static Lensed Troffer is a specification grade recessed lensed luminaire and offers many premium options.

Product data

General Information	
Lamp Envelope Code	T-8
Lamp Source Code	Fluorescent
Lamp Watts	32
Number of Lamps	4
Mounting	Recessed
Operating and Electrical	
Voltages	120/277/347 V
Mechanical and Housing	
Fixture Size	2 ft x 4 ft
Product Data	
Order product name	2SPG432-FS12-UNV

EAN/UPC - Product	781370713430
Order code	912400371630
Local order code	7071343
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400371630
Net Weight (Piece)	10.300 kg
Commercial Code	2SPG432-FS12-UNV-1/4-EB10R
Catalog Number Description	2x4, 4 Lamp F32T8, Prismatic Acrylic Lens
Quick Ship	-