



SP Static Recessed Lensed

2SPG317R-FS12-UNV

2x2, 3 Lamp F17T8, Prismatic Acrylic Lens

The SP Static Lensed Troffer is a specification grade recessed lensed luminaire and offers many premium options.

Product data

General Information	
Lamp Envelope Code	T-8
Lamp Source Code	Fluorescent
Lamp Watts	17
Number of Lamps	3
Mounting	Recessed
Operating and Electrical	
Voltages	120/277/347 V
Mechanical and Housing	
Fixture Size	2 ft x 2 ft
Product Data	
Order product name	2SPG317R-FS12-UNV

EAN/UPC - Product	781370793807
Order code	912400372137
Local order code	7079380
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400372137
Net Weight (Piece)	0.001 kg
Commercial Code	2SPG317R-FS12-UNV-1/3-EB
Catalog Number Description	2x2, 3 Lamp F17T8, Prismatic Acrylic Lens
Quick Ship	-