



Arioso Recessed

2x2, 2 Lamp CF40, 2-Piece Perforated Metal Shield & White Overlay

2x2, 2 Lamp CF40, 2-Piece Perforated Metal Shield & White Overlay

Arioso Recessed offers simple clean lines in combination with soft natural illumination. This series focuses on providing smooth comfortable lighting while subtly complementing the space. Flexible enough to integrate with any architectural design, Arioso Recessed provides a soft unassuming glow with comfortable illumination.

Product data

General Information	
Lamp Envelope Code	TT5
Lamp Source Code	Compact Fluorescent
Lamp Watts	40
Number of Lamps	2
Photometric Distribution Type	Direct
Mounting	Recessed
Operating and Electrical	
Voltages	UNIV V
Luminaire Input Watts	67
Mechanical and Housing	
Fixture Size	2 ft x 2 ft
Shape	Square

Product Data	
Order product name	2AVG2CF40-SPMW-UNV
EAN/UPC - Product	781370868871
Order code	2AVG2CF40-SPMW-UNV-1/2-EB
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400372552
Net Weight (Piece)	8.199 kg
Catalog Number	2AVG2CF40-SPMW-UNV-1/2-EB
Catalog Number Description	2x2, 2 Lamp CF40, 2-Piece Perforated Metal Shield & White Overlay