



# DuaLED Surface LED

## 2SDL58L840-4-D-UNV

2x4, 5800 Nominal Delivered Lumens, 4000K, Surface Mount,  
Diffuse - 100 lm/W

Surface DuaLED was thoughtfully developed as a sustainable luminaire with a modern appearance and uncomplicated design, also offering exceptional quality and performance, for an outstanding benefit to the customer. DuaLED is a highly efficient, architecturally styled recessed LED luminaire designed with a minimalistic strategy to achieve sustainable objectives. It combines an extremely low profile with clean aesthetics and is powered by highly efficient advanced LED sources, providing the utmost in comfortable efficient lighting. Driver and integral control options ensure optimization for every application. Designed for excellent visual comfort, DuaLED is perfect for a wide variety of general applications like offices, schools, retail, or healthcare. Optional SpaceWise automated wireless technology provides integrated occupancy and daylight harvesting for additional control and energy savings with no reduction of life.

### Product data

General Information	
Lamp Source Code	LED
Color Temperature	4000K
CRI	80
Photometric Distribution Type	Direct
Mounting	Surface
Operating and Electrical	
Voltages	120/277/347 V
Luminaire Input Watts	58

Mechanical and Housing	
Fixture Size	2 ft x 4 ft
Shape	Rectangular
Initial Performance (IEC Compliant)	
Luminaire Lumens	5800
Efficacy	100 lm/W
Product Data	
Order product name	2SDL58L840-4-D-UNV
EAN/UPC - Product	734340039177
Order code	912400381715

DuaLED Surface LED

Local order code	4003917
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400381715
Net Weight (Piece)	8.100 kg
Commercial Code	2SDL58L840-4-D-UNV-DIM

Catalog Number	Description
	2x4, 5800 Nominal Delivered Lumens, 4000K, Surface Mount, Diffuse
Quick Ship	-

