



DuaLED Recessed

2DLG58L840-4-D-UNV

2x4, 5800 Nominal Delivered Lumens, 4000K, Diffuse - 100 lm/W

DuaLED was thoughtfully developed as a sustainable luminaire with a modern appearance and uncomplicated design, also offering exceptional quality and performance, for an outstanding benefit to the customer. DuaLED is a highly efficient, architecturally styled recessed LED luminaire designed with a minimalistic strategy to achieve sustainable objectives. It combines an extremely low profile with clean aesthetics and is powered by highly efficient advanced LED sources, providing the utmost in comfortable efficient lighting. Driver and integral control options ensure optimization for every application. Designed for excellent visual comfort, DuaLED is perfect for a wide variety of general applications like offices, schools, retail, or healthcare.

Product data

General Information	
Lamp Source Code	LED
Color Temperature	4000K
CRI	80
Photometric Distribution Type	Direct
Mounting	Recessed
Operating and Electrical	
Voltages	120/277/347 V
Luminaire Input Watts	58
Mechanical and Housing	
Fixture Size	2 ft x 4 ft
Shape	Rectangular

Initial Performance (IEC Compliant)	
Luminaire Lumens	5800
Efficacy	100 lm/W
Product Data	
Order product name	2DLG58L840-4-D-UNV
EAN/UPC - Product	782343496763
Order code	912400383682
Local order code	4349676
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400383682
Net Weight (Piece)	0.001 kg
Commercial Code	2DLG58L840-4-D-UNV-DIM
Catalog Number Description	2x4, 5800 Nominal Delivered Lumens, 4000K, Diffuse
Quick Ship	Spec Smart (10 Days) USA

