



CRC Series Surface Cleanroom

2 Lamp F32T8, 125 Prismatic Acrylic Lens

2 Lamp F32T8, 125 Prismatic Acrylic Lens

The CRC Containment Series is designed to meet the criteria for critical environments in coner mount applications.

Product data

General Information	
Lamp Envelope Code	T-8
Lamp Source Code	Fluorescent
Lamp Watts	32
Number of Lamps	2
Mounting	Surface
Operating and Electrical	
Voltages	120/277/347 V
Mechanical and Housing	
Shape	Linear

Product Data	
Order product name	CRC232-UNV
EAN/UPC - Product	782343156131
Order code	CRC232-UNV-A-1/2-EB
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400389216
Net Weight (Piece)	0.001 kg
Catalog Number	CRC232-UNV-A-1/2-EB
Catalog Number Description	2 Lamp F32T8, 125 Prismatic Acrylic Lens