



LSW

LS4R154UNV

Ceiling Or Wall Mounted Fluorescent, 6" Width, 3 7/8" Deep, One lamp 54 watt T5 48" length luminaire

LSW Lens Wrap Ceiling/Wall Mounted - Specification Grade For ceiling or wall (vertically or horizontally) mounted applications. Only 3 7/8" deep, meets Americans with Disabilities Act (wall mounted). Low brightness .125 thick linear prismatic virgin acrylic refractor. Invisible spring steel latches align refractor to housing. 2 gauge cold rolled steel post painted baked white enamel end caps. For over mirror, over bed, corridor, stairwell and bulletin board applications.

Product data

| | | | |
|---------------------------------|--------------|---------------------------------|--|
| General Information | | EAN/UPC - Product | 782343156049 |
| Lamp Envelope Code | T-5 | Order code | 912400392230 |
| Lamp Watts | 54 | Local order code | 4315604 |
| Number of Lamps | 1 | Numerator - Quantity Per Pack | 1 |
| Mounting | Wall Surface | Numerator - Packs per outer box | 1 |
| Operating and Electrical | | Material Nr. (12NC) | 912400392230 |
| Voltages | 277 V | Net Weight (Piece) | 0.001 kg |
| Mechanical and Housing | | Commercial Code | LS4R154UNVPG |
| Fixture Size | 48 in | Catalog Number Description | Ceiling Or Wall Mounted Fluorescent, 6" Width, 3 7/8" Deep, One lamp 54 watt T5 48" length luminaire |
| Product Data | | | |
| Order product name | LS4R154UNV | | |