



LSW

Ceiling Or Wall Mounted Fluorescent, 6" Width, 3 7/8" Deep, One lamp 54 watt T5 48" length luminaire

Ceiling Or Wall Mounted Fluorescent, 6" Width, 3 7/8" Deep, One lamp 54 watt T5 48" length luminaire

LSW Lens Wrap Ceiling/Wall Mounted - Specification Grade For ceiling or wall (vertically or horizontally) mounted applications. Only 3 7/8" deep, meets Americans with Disabilities Act (wall mounted). Low brightness .125 thick linear prismatic virgin acrylic refractor. Invisible spring steel latches align refractor to housing. 2 gauge cold rolled steel post painted baked white enamel end caps. For over mirror, over bed, corridor, stairwell and bulletin board applications.

Product data

General Information		EAN/UPC - Product 782343156049	
Lamp Envelope Code	T-5	Order code	LS4R154UNVPG
Lamp Watts	54	Numerator - Quantity Per Pack	1
Number of Lamps	1	Numerator - Packs per outer box	1
Mounting	Wall Surface	Material Nr. (12NC)	912400392230
Operating and Electrical		Net Weight (Piece)	0.001 kg
Voltages	277 V	Catalog Number	LS4R154UNVPG
Mechanical and Housing		Catalog Number Description	Ceiling Or Wall Mounted Fluorescent, 6" Width, 3 7/8" Deep, One lamp 54 watt T5 48" length luminaire
Fixture Size	48 in		
Product Data			
Order product name	LS4R154UNV		