



# Arioso Recessed LED

## 2AVEG38L835-4-ACR-UNV

2x4, 3800 Nominal Delivered Lumens, 3500K, Frosted Acrylic Lens - 94 lm/W

The Philips Day-Brite / Philips CFI Arioso Recessed LED offers standard-setting efficiency without aesthetic compromise. These LED luminaires combine state-of-the-art, flexible and globally- recognized LED lighting platforms with proven Arioso optical combinations.

### Product data

General Information	
Lamp Source Code	LED
Color Temperature	3500K
CRI	80
Photometric Distribution Type	Direct
Mounting	Recessed
Operating and Electrical	
Voltages	UNIV V
Luminaire Input Watts	40.5
Mechanical and Housing	
Fixture Size	2 ft x 4 ft
Shape	Rectangular
Initial Performance (IEC Compliant)	
Luminaire Lumens	3800

Efficacy	94 lm/W
Product Data	
Order product name	2AVEG38L835-4-ACR-UNV
EAN/UPC - Product	782343164310
Order code	912400392284
Local order code	4316431
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400392284
Net Weight (Piece)	0.001 kg
Commercial Code	2AVEG38L835-4-ACR-UNV
Catalog Number Description	2x4, 3800 Nominal Delivered Lumens, 3500K, Frosted Acrylic Lens
Quick Ship	-