



# DuaLED Surface LED

## 2SDL49L840-4-D-UNV

2x4, 4900 Nominal Delivered Lumens, 4000K, Surface Mount,  
Diffuse - 102 lm/W

Surface DuaLED was thoughtfully developed as a sustainable luminaire with a modern appearance and uncomplicated design, also offering exceptional quality and performance, for an outstanding benefit to the customer. DuaLED is a highly efficient, architecturally styled recessed LED luminaire designed with a minimalistic strategy to achieve sustainable objectives. It combines an extremely low profile with clean aesthetics and is powered by highly efficient advanced LED sources, providing the utmost in comfortable efficient lighting. Driver and integral control options ensure optimization for every application. Designed for excellent visual comfort, DuaLED is perfect for a wide variety of general applications like offices, schools, retail, or healthcare. Optional SpaceWise automated wireless technology provides integrated occupancy and daylight harvesting for additional control and energy savings with no reduction of life.

### Product data

General Information	
Lamp Source Code	LED
Color Temperature	4000K
CRI	80
Photometric Distribution Type	Direct
Mounting	Surface
Operating and Electrical	
Voltages	120/277/347 V
Luminaire Input Watts	48

Mechanical and Housing	
Fixture Size	2 ft x 4 ft
Shape	Rectangular
Initial Performance (IEC Compliant)	
Luminaire Lumens	4900
Efficacy	102 lm/W
Product Data	
Order product name	2SDL49L840-4-D-UNV
EAN/UPC - Product	734340162240
Order code	912400394822

DuaLED Surface LED

Local order code	4016224
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400394822
Net Weight (Piece)	0.001 kg
Commercial Code	2SDL49L840-4-D-UNV-DIM

Catalog Number Description	2x4, 4900 Nominal Delivered Lumens, 4000K, Surface Mount, Diffuse
Quick Ship	-

