



DuaLED Surface LED

1SDL41L840-4-D-UNV

1x4, 4100 Nominal Delivered Lumens, 4000K, Surface Mount, Diffuse - 93 lm/W

Surface DuaLED was thoughtfully developed as a sustainable luminaire with a modern appearance and uncomplicated design, also offering exceptional quality and performance, for an outstanding benefit to the customer. DuaLED is a highly efficient, architecturally styled recessed LED luminaire designed with a minimalistic strategy to achieve sustainable objectives. It combines an extremely low profile with clean aesthetics and is powered by highly efficient advanced LED sources, providing the utmost in comfortable efficient lighting. Driver and integral control options ensure optimization for every application. Designed for excellent visual comfort, DuaLED is perfect for a wide variety of general applications like offices, schools, retail, or healthcare. Optional SpaceWise automated wireless technology provides integrated occupancy and daylight harvesting for additional control and energy savings with no reduction of life.

Product data

General Information		Mechanical and Housing	
Lamp Source Code	LED	Fixture Size	1 ft x 4 ft
Color Temperature	4000K	Shape	Rectangular
CRI	80	Initial Performance (IEC Compliant)	
Photometric Distribution Type	Direct	Luminaire Lumens	4100
Mounting	Surface	Efficacy	93 lm/W
Operating and Electrical		Product Data	
Voltages	120/277/347 V	Order product name	1SDL41L840-4-D-UNV
Luminaire Input Watts	44	EAN/UPC - Product	734340984767
		Order code	912400397849

DuaLED Surface LED

Local order code	4098476
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400397849
Net Weight (Piece)	0.001 kg
Commercial Code	1SDL41L840-4-D-UNV-DIM

Catalog Number	Description	1x4, 4100 Nominal Delivered Lumens, 4000K, Surface Mount, Diffuse
Quick Ship		-

