



# Arioso Recessed LED

## 2x2, 3800 Nominal Delivered Lumens, 3500K, Frosted Acrylic Lens

2x2, 3800 Nominal Delivered Lumens, 3500K, Frosted Acrylic Lens

The Day-Brite / CFI Arioso Recessed LED offers standard-setting efficiency without aesthetic compromise. These LED luminaires combine state-of-the-art, flexible and globally- recognized LED lighting platforms with proven Arioso optical combinations.

### Product data

General information	
Lamp Source Code	LED
Colour Temperature	3500 K
CRI	80
Photometric Distribution Type	Direct
Mounting	Recessed
Operating and electrical	
Voltages	UNIV V
Luminaire Input Watts	40
Mechanical and housing	
Fixture Size	2 ft x 2 ft
Shape	Square
Initial performance (IEC compliant)	
Luminaire Lumens	3800

Product data	
Order product name	2AVEG38L835-2-ACR-UNV
EAN/UPC - Product	781370404017
Order code	2AVEG38L835-2-ACR-UNV-DIM
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400399087
Net Weight (Piece)	0.001 kg
Catalog Number	2AVEG38L835-2-ACR-UNV-DIM
Catalog Number Description	2x2, 3800 Nominal Delivered Lumens, 3500K, Frosted Acrylic Lens