



BL616 Micro Accent

Accent, Aluminum Bullyte w/ Stake, Black, 7W LED, Flood, 2700K, 12V

Accent, Aluminum Bullyte w/ Stake, Black, 7W LED, Flood, 2700K, 12V

The BL616 is made with die-cast aluminum and has a fully adjustable swivel arm with vibration-proof locking teeth. Available in low voltage incandescent and LED sources.

Product data

General Information	
Lamp Source Code	LED
Lamp Watts	7
Number of Lamps	1
Colour Temperature	3000K
CRI	80
Photometric Distribution Type	Wide Flood
Mounting	NPT/NPS
Operating and Electrical	
Voltages	12 V
Luminaire Input Watts	7
Initial Performance (IEC Compliant)	
Luminaire Lumens	600

Product Data	
Order product name	BULLYTE,MICRO W/STAKE
EAN/UPC - Product	046677323769
Order code	BL616-AS7LED7FLW
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400446875
Net Weight (Piece)	0.001 kg
Catalog Number	BL616-AS7LED7FLW
Catalog Number Description	Accent, Aluminum Bullyte w/ Stake, Black, 7W LED, Flood, 2700K, 12V