



Roughlyte Vaportight

VCXL42HFL-8

CFL, 42W, 120-277V, Roughlyte

The Roughlyte Compact Fluorescent Series is available in 26, 32 and 42 watt lamps. Applications include restaurants, taverns or nightclubs, food courts, atriums or plazas, malls, retail outlets, stores, athletic clubs and facilities, theatres, arenas, stadiums and amusement parks. Heat and shock resistant, prismatic glass optical chamber with neoprene gasketing. Low-glare clear prismatic glass globe standard. Approximately 40% uplight. UL 1598 listed for wet locations – Globe down only. Not recommended for hazardous locations.;

The Roughlyte Incandescent Series is available in wattages ranging from 75 to 200. Applications include wall, columns, ceilings and canopys in exterior applications. Roughlyte fixtures guard against moisture and debris in exterior applications (for globe down mounting only). Features include heat and shock resistant glass or polycarbonate globe and cast aluminum bayonet guard with Allen head security screws. Not recommended for hazardous locations.

Product data

General Information		EAN/UPC - Product	
Lamp Source Code	Compact Fluorescent	Order code	VCXL42HFL-8
Lamp Watts	42	Local order code	.
Number of Lamps	1	Numerator - Quantity Per Pack	1
Photometric Distribution Type	Type V	Numerator - Packs per outer box	1
Mounting	Surface	Material Nr. (12NC)	912400477179
Operating and Electrical		Net Weight (Piece)	2177.242 g
Voltages	120/208/240/277 V	Commercial Code	VCXL42HFL-8
Product Data		Catalog Number Description	CFL, 42W, 120-277V, Roughlyte
Order product name	VCXL42HFL-8	Quick Ship	-