



# WPM Wall Pack Medium

## HPS, 150W, 120-277V, w/Lamp, Wall-Pack

HPS, 150W, 120-277V, w/Lamp, Wall-Pack

The Wallprism Series includes four different sized surface mount HID/CF luminaires for security, accent and perimeter lighting. A patented catadioptric refractor redirects light to minimize glare, aligns optical center of lens and lamp for symmetrical light distribution. Sizes and maximum wattage range from WNPS (100W), WPM (300W), WP (500) and DB (400). Select models include high lumen output LEDs with 50,000 lifetime operating hours and induction that provides low maintenance and 100,000 lifetime operating hours.

### Product data

General Information		EAN/UPC - Product	
Lamp Source Code	High Pressure Sodium	Order code	WPM150LXL-8
Lamp Watts	150	Numerator - Quantity Per Pack	1
Number of Lamps	1	Numerator - Packs per outer box	1
Photometric Distribution Type	Type IV	Material Nr. (12NC)	912400477243
Mounting	Wall	Net Weight (Piece)	0.001 kg
Operating and Electrical		Catalog Number	WPM150LXL-8
Voltages	120/208/240/277 V	Catalog Number Description	HPS, 150W, 120-277V, w/Lamp, Wall-Pack
Product Data			
Order product name	WPM150LX-8 W/LAMP (SPECIAL)		