



# GP Flood Series - GP4

HPS, 400W, 120-277V, w/Lamp, Slipfitter, Flood

HPS, 400W, 120-277V, w/Lamp, Slipfitter, Flood

The GP4 Flood Series combines architectural design with on-site versatility and is designed for general purpose floodlighting installations. Applications include security, roadway, area, accent, facade, recreational fields, flagpole, and sign lighting. The GP4 Flood series is available with ED28 lamps for pulse start metal halide and ED18 lamps for high pressure sodium up to 400 watts. Reflectors include general purpose, spot and cut-off optics for control of light trespass. IP65 Rated for extra protection against water, dust and debris, and can be aimed above or below horizontal. The GP4 is also available in 55W and 85W very-long life induction sources for 100,000 hours.

## Product data

General Information	
Lamp Source Code	High Pressure Sodium
Lamp Watts	400
Number of Lamps	1
Photometric Distribution Type	Flood
Mounting	Ground / Floor

  

Operating and Electrical	
Voltages	120/208/240/277 V
Maximum Lamp Watts	400

  

Product Data	
Order product name	GP4S400LXL-8

  

EAN/UPC - Product	190096002368
Order code	GP4S400LXL-8
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400478447
Net Weight (Piece)	13471.682 g
Catalog Number	GP4S400LXL-8
Catalog Number Description	HPS, 400W, 120-277V, w/Lamp, Slipfitter, Flood