



GP Flood Series - GP2

PS, 100W, 120/277V, w/Lamp, Flood

PS, 100W, 120/277V, w/Lamp, Flood

The GP2 Flood Series combines architectural design with on-site versatility and is designed for general purpose floodlighting installations. Applications include security, roadway, area, accent, facade, recreational fields, flagpole, and sign lighting. The GP2 Flood series is available with ED17 lamps for pulse start metal halide and B17 lamps for high pressure sodium up to 175 watts. Reflectors include general purpose, spot and cut-off optics for control of light trespass. IP65 Rated for extra protection against water, dust and debris, and can be aimed above or below horizontal. The LED version is available in 30 LEDs in either 40W or 60W configurations.

Product data

General Information		EAN/UPC - Product	
Lamp Source Code	Pulse Start Metal Halide	Order code	GP2A100PMAL-6
Lamp Watts	100	Numerator - Quantity Per Pack	1
Number of Lamps	1	Numerator - Packs per outer box	1
Photometric Distribution Type	NEMA 7H x 7V	Material Nr. (12NC)	912400480745
Mounting	Ground / Floor	Net Weight (Piece)	0.001 kg
Operating and Electrical		Catalog Number	GP2A100PMAL-6
Voltages	120/277 V	Catalog Number Description	PS, 100W, 120/277V, w/Lamp, Flood
Maximum Lamp Watts	100		
Product Data			
Order product name	GP2A100PMAL-6		