



# GP Flood Series - GP2

## HPS, 150W, 120V, w/Lamp, Flood

HPS, 150W, 120V, w/Lamp, Flood

The GP2 Flood Series combines architectural design with on-site versatility and is designed for general purpose floodlighting installations. Applications include security, roadway, area, accent, facade, recreational fields, flagpole, and sign lighting. The GP2 Flood series is available with ED17 lamps for pulse start metal halide and B17 lamps for high pressure sodium up to 175 watts. Reflectors include general purpose, spot and cut-off optics for control of light trespass. IP65 Rated for extra protection against water, dust and debris, and can be aimed above or below horizontal. The LED version is available in 30 LEDs in either 40W or 60W configurations.

### Product data

General Information		EAN/UPC - Product	
Lamp Source Code	High Pressure Sodium	Order code	GP2A150NLXL-1
Lamp Watts	150	Numerator - Quantity Per Pack	1
Number of Lamps	1	Numerator - Packs per outer box	1
Photometric Distribution Type	NEMA 7H x 6V	Material Nr. (12NC)	912400480747
Mounting	Ground / Floor	Net Weight (Piece)	0.010 kg
Operating and Electrical		Catalog Number	GP2A150NLXL-1
Voltages	120 V	Catalog Number Description	HPS, 150W, 120V, w/Lamp, Flood
Maximum Lamp Watts	150		
Product Data			
Order product name	GP2A,150W,HPS,NPF,LAMP,120V		