



# GP Flood Series - GP2

PS, 70W, 120/277V, Cutoff Optics, w/Lamp, Flood

PS, 70W, 120/277V, Cutoff Optics, w/Lamp, Flood

The GP2 Flood Series combines architectural design with on-site versatility and is designed for general purpose floodlighting installations. Applications include security, roadway, area, accent, facade, recreational fields, flagpole, and sign lighting. The GP2 Flood series is available with ED17 lamps for pulse start metal halide and B17 lamps for high pressure sodium up to 175 watts. Reflectors include general purpose, spot and cut-off optics for control of light trespass. IP65 Rated for extra protection against water, dust and debris, and can be aimed above or below horizontal. The LED version is available in 30 LEDs in either 40W or 60W configurations.

## Product data

| General Information           |                          | EAN/UPC - Product               |   |
|-------------------------------|--------------------------|---------------------------------|---|
| Lamp Source Code              | Pulse Start Metal Halide | Order code                      | GP2A70PMALC-6                                   |
| Lamp Watts                    | 70                       | Numerator - Quantity Per Pack   | 1   |
| Number of Lamps               | 1                        | Numerator - Packs per outer box | 1   |
| Photometric Distribution Type | Flood                    | Material Nr. (12NC)             | 912400480751                                    |
| Mounting                      | Ground / Floor           | Net Weight (Piece)              | 0.010 kg  |
| Operating and Electrical      |                          | Catalog Number                  | GP2A70PMALC-6                                   |
| Voltages                      | 120/277 V                | Catalog Number Description      | PS, 70W, 120/277V, Cutoff Optics, w/Lamp, Flood |
| Maximum Lamp Watts            | 70                       |                                 |   |
| Product Data                  |                          |                                 |   |
| Order product name            | GP2A70PMALC-6            |                                 |   |