



# GP Flood Series - GP3

## GP3,320W,PSMH,QUAD,SLIPFITTER,W/ LAMP

PS, 320W, 120-277V, w/Lamp, Slipfitter, Flood

The GP3 Flood Series combines architectural design with on-site versatility and is designed for general purpose floodlighting installations. Applications include security, roadway, area, accent, facade, recreational fields, flagpole, and sign lighting. The GP3 Flood series is available with ED28 lamps for pulse start metal halide and ED18 lamps for high pressure sodium up to 400 watts. Reflectors include general purpose, spot and cut-off optics for control of light trespass. IP65 Rated for extra protection against water, dust and debris, and can be aimed above or below horizontal. The LED version is available in 49 LEDs and a 103W configuration.

### Product data

General Information		EAN/UPC - Product	
Lamp Source Code	Pulse Start Metal Halide	Order code	GP3S320PMAL-8
Lamp Watts	320	Local order code	.
Number of Lamps	1	Numerator - Quantity Per Pack	1
Photometric Distribution Type	NEMA 6H x 6V	Numerator - Packs per outer box	1
Mounting	Ground / Floor	Material Nr. (12NC)	912400480755
Operating and Electrical		Net Weight (Piece)	9525.432 g
Voltages	120/208/240/277 V	Commercial Code	GP3S320PMAL-8
Maximum Lamp Watts	320	Catalog Number Description	PS, 320W, 120-277V, w/Lamp, Slipfitter, Flood
Product Data		Quick Ship	-
Order product name	GP3,320W,PSMH,QUAD,SLIPFITTER,W/ LAMP		