



# GP Flood Series - GP4

PS, 250W, 120-277V, w/Lamp, Slipfitter, Flood

PS, 250W, 120-277V, w/Lamp, Slipfitter, Flood

The GP4 Flood Series combines architectural design with on-site versatility and is designed for general purpose floodlighting installations. Applications include security, roadway, area, accent, facade, recreational fields, flagpole, and sign lighting. The GP4 Flood series is available with ED28 lamps for pulse start metal halide and ED18 lamps for high pressure sodium up to 400 watts. Reflectors include general purpose, spot and cut-off optics for control of light trespass. IP65 Rated for extra protection against water, dust and debris, and can be aimed above or below horizontal. The GP4 is also available in 55W and 85W very-long life induction sources for 100,000 hours.

## Product data

General Information		EAN/UPC - Product	
Lamp Source Code	Pulse Start Metal Halide	Order code	GP4S250PMAL-8
Lamp Watts	250	Numerator - Quantity Per Pack	1
Number of Lamps	1	Numerator - Packs per outer box	1
Photometric Distribution Type	NEMA 6H x 6V	Material Nr. (12NC)	912400480765
Mounting	Ground / Floor	Net Weight (Piece)	0.010 kg
Operating and Electrical		Catalog Number	GP4S250PMAL-8
Voltages	120/208/240/277 V	Catalog Number Description	PS, 250W, 120-277V, w/Lamp, Slipfitter, Flood
Maximum Lamp Watts	250		
Product Data			
Order product name	GP4S252PMAL-8		